



# stellar

## Product Specifications

### Stellar Polyurethane Aprons



#### Measurements

| Material     | Thickness | Width | Case Length (mm) | Case Width (mm) | Case Height (mm) |
|--------------|-----------|-------|------------------|-----------------|------------------|
| Polyurethane | 5.5 mil   | 35.5" | 359              | 245             | 114              |

| Item #        | Colour | Length | Style      | Apron Weight (g) | Case weight (kg) |
|---------------|--------|--------|------------|------------------|------------------|
| 032-E15695-WH | White  | 45"    | Die Cut    | 164              | 3.9              |
| 032-E15695-BU | Blue   | 45"    | Die Cut    | 164              | 3.9              |
| 032-E15695-YE | Yellow | 45"    | Die Cut    | 164              | 3.9              |
| 032-E15695-RE | Red    | 45"    | Die Cut    | 164              | 3.9              |
| 032-E15698-WH | White  | 50"    | Die Cut    | 181              | 4.3              |
| 032-E15698-BU | Blue   | 50"    | Die Cut    | 181              | 4.3              |
| 032-E15698-YE | Yellow | 50"    | Die Cut    | 181              | 4.3              |
| 032-E15698-RE | Red    | 50"    | Die Cut    | 181              | 4.3              |
| 032-E15795-WH | White  | 45"    | Adjustable | 212              | 5.1              |
| 032-E15795-BU | Blue   | 45"    | Adjustable | 212              | 5.1              |
| 032-E15795-YE | Yellow | 45"    | Adjustable | 212              | 5.1              |
| 032-E15798-WH | White  | 50"    | Adjustable | 233              | 5.6              |
| 032-E15798-BU | Blue   | 50"    | Adjustable | 233              | 5.6              |
| 032-E15798-YE | Yellow | 50"    | Adjustable | 233              | 5.6              |

Packaging: 24 Aprons/ Case

Country of Origin: Canada

Acceptances: Comply with CFIA and FDA guidelines

Care instructions:

Stellar Polyurethane PPEs are very easy to wash as they washer & dryer safe.

It can go through up to 200 industrial washings without changing properties.

You can use commercial laundry detergent, soap or disinfectant (e.g. wash in temp. up to 100F/ 38C)

You may tumble dry at low heat or hang to dry.



MADE IN CANADA  
FABRIQUÉ AU CANADA



LATEX FREE



NON-STERILE

### Stellar Safety Supply

[www.stellarsafetysupply.com](http://www.stellarsafetysupply.com)

1.855.738.1006